

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	260328 10/07
GTIN	4045197652799
Item class	21T

Technical description

Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	13 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	AH10K SDQCR/L07
Insert size	7 mm
Centre offset L_3	7 mm
Head length L_1	20 mm
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500