

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	260333 10/07
GTIN	4045197652980
Item class	21T

Description

Boring bar HSS 10/07 mm Shank \varnothing D_s: 10 mm
 ISO code toolholder: AH10K SDUCR/L07
 Setting angle κ : 93 °
 suitable indexable insert: DC.. 0702..
 Minimum pre-drill \varnothing D_{min}: 14 mm
 Centre offset L₃: 9 mm

Technical description

ISO code toolholder	AH10K SDUCR/L07
suitable indexable insert	DC.. 0702..
Centre offset L ₃	9 mm
Insert size	7 mm
Overhang L ₁	50 mm
Pack of insert screws	269028 7
Minimum pre-drill \varnothing D _{min}	14 mm
Overall length L	125 mm
Clamping height L ₂	9 mm
Setting angle κ	93 °
Shank \varnothing D _s	10 mm
Application type	left-hand

Boring depth up to	5×D
Tool material	HSS
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500