

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 8/07mm

Order data

Order number	260319 8/07
GTIN	4045197652706
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	7 mm
Centre offset L_3	7.5 mm
ISO code toolholder	E08K SDUCR/L07
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
suitable indexable insert	DC.. 0702..
Overall length L	125 mm
Clamping height L_2	7.6 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500