

**Garant**
**GARANT Master Eco boring bar holder Form E2, VDI 40, Bore dia. d2 (H7): 12mm**

**Order data**

Order number	319235 12
GTIN	4067263108016
Item class	31V

**Description**
**Version:**

- Case-hardened HRC 58+/-2.
- All functional faces ground.
- Through-bored VDI shank.
- With two ball spray nozzles.

**Advantage:**

- Also suitable for longer boring bars.
- Individual length adjustment for the boring bars.

**Application:**

For internal machining with boring bar holder.

**Technical description**

Bore d <sub>2</sub> (H7)	12 mm
Ø L <sub>6</sub>	75 mm
Ø L <sub>7</sub>	110.5 mm
Ø H <sub>1</sub>	32.5 mm
Ø H <sub>3</sub>	21.5 mm
Ø D <sub>6</sub>	83 mm

Ø L <sub>3</sub>	22 mm
Ø D <sub>8</sub>	65 mm
Shape	E
VDI size	VDI 40
d <sub>7</sub>	20.5 mm
Colour code for VDI shanks	VDI 40
Type of product	VDI boring bar toolholder