

Garant
GARANT Master Eco boring bar holder Form E2, VDI 30, Bore dia. d2 (H7): 32mm

Order data

Order number	319225 32
GTIN	4067263107880
Item class	31V

Description
Version:

- Case-hardened HRC 58+/-2.
- All functional faces ground.
- Through-bored VDI shank.
- With two ball spray nozzles.

Advantage:

- Also suitable for longer boring bars.
- Individual length adjustment for the boring bars.

Application:

For internal machining with boring bar holder.

Technical description

Bore d ₂ (H7)	32 mm
Ø H ₃	31 mm
Ø H ₁	28 mm
Ø D ₈	67 mm
Ø D ₆	68 mm
Ø L ₇	51 mm

Ø L ₆	80 mm
Ø L ₃	22 mm
Shape	E
VDI size	VDI 30
d ₇	16.5 mm
Colour code for VDI shanks	VDI 30
Type of product	VDI boring bar toolholder