

Garant
GARANT Master Eco boring bar holder Form E2, VDI 40, Bore dia. d2 (H7): 50mm

Order data

Order number	319235 50
GTIN	4067263108108
Item class	31V

Description
Version:

- Case-hardened HRC 58+/-2.
- All functional faces ground.
- Through-bored VDI shank.
- With two ball spray nozzles.

Advantage:

- Also suitable for longer boring bars.
- Individual length adjustment for the boring bars.

Application:

For internal machining with boring bar holder.

Technical description

Bore d ₂ (H7)	50 mm
Ø H ₁	32.5 mm
Ø L ₃	22 mm
Ø D ₈	92 mm
Ø L ₇	86 mm
Ø D ₆	98 mm

Ø L ₆	100 mm
Ø H ₃	39.5 mm
Shape	E
VDI size	VDI 40
d ₇	20.5 mm
Colour code for VDI shanks	VDI 40
Type of product	VDI boring bar toolholder