



Boring bar steel, right-hand, Shank \varnothing / insert size: 16/07mm



Order data

Order number	260338 16/07
GTIN	
Item class	25U

Description

Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

Technical description

Centre offset L_3	11.7 mm
ISO code toolholder	A16Q SDUCR/L07
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Overhang L_1	80 mm
Insert size	7 mm
Insert screw	269022 4
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Application type	right-hand
Boring depth up to	5xD
Standard	DIN 8024
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Insert screw Type 4	269022 4