

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 0810/07mm

Order data

Order number	260332 0810/07
GTIN	4045197652898
Item class	21T

Technical description

Neck width L_4	8 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Head length L_1	22 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Insert size	7 mm
Centre offset L_3	7 mm
ISO code toolholder	AH0810H SDUCR/L07
Overall length L	100 mm
Clamping height L_2	9 mm
Setting angle κ	93 degrees
Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500