

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	260328 20/11
GTIN	4045197652829
Item class	21T

Technical description

ISO code toolholder	AH20R SDQCR/L11
Centre offset L_3	12.5 mm
Head length L_1	40 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500