

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	260333 12/07
GTIN	4045197653000
Item class	21T

Technical description

Insert size	7 mm
ISO code toolholder	AH12M SDUCR/L07
Pack of insert screws	269028 7
Centre offset L_3	8 mm
Minimum pre-drill $\varnothing D_{\min}$	16 mm
suitable indexable insert	DC.. 0702..
Overhang L_1	60 mm
Overall length L	150 mm
Clamping height L_2	11 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500