

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 1216/07mm

Order data

Order number	260333 1216/07
GTIN	4045197653017
Item class	21T

Technical description

Insert size	7 mm
Neck width L_4	12 mm
Centre offset L_3	11 mm
Head length L_1	36 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	AH1216M SDUCR/L07
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Pack of insert screws	269028 7
Overall length L	150 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500