


WNMG 080408, Grade: CA6525

Order data

| | |
|--------------|---------------|
| Order number | 252014 CA6525 |
| GTIN | 4960664513239 |
| Item class | 25E |

Description

WNMG 080408 CA6525 Grade: CA6525

Chip breaker: MQ

Cutting depth a_p : 0.3 - 2 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 60 - 220 m/min

Technical description

| | |
|--------------------------------------|----------------------|
| Feed f | 0.05 - 0.25 mm/rev. |
| Main application | M |
| Cutting depth a_p | 0.3 - 2 mm |
| Cutting conditions | slightly interrupted |
| Corner radius | 0.8 mm |
| Cutting speed v_c main application | 60 - 220 m/min |
| Chip breaker | MQ |
| Grade | CA6525 |

| | |
|-------------------------------|------------------------------|
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | WNMG 080408 |
| Number of changes/inserts | 6 |
| Type of product | Indexable insert for turning |