

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	260319 16/07
GTIN	4045197652737
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	19 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
ISO code toolholder	E16R SDUCR/L07
Insert size	7 mm
Centre offset L_3	11 mm
Overall length L	200 mm
Clamping height L_2	15.6 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500