

**Garant**
**Boring bar HSS, right-hand, Shank  $\varnothing$  / insert size: 1216/07mm**

**Order data**

Order number	260332 1216/07
GTIN	4045197652935
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
Centre offset $L_3$	11 mm
ISO code toolholder	AH1216M SDUCR/L07
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Neck width $L_4$	12 mm
Head length $L_1$	36 mm
Insert size	7 mm
Overall length L	150 mm
Clamping height $L_2$	15 mm
Setting angle $\kappa$	93 degrees
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500