

**Garant**
**Boring bar HSS, right-hand, Shank  $\varnothing$  / insert size: 16/07mm**

**Order data**

Order number	260332 16/07
GTIN	4045197652942
Item class	21T

**Technical description**

Overhang $L_1$	80 mm
suitable indexable insert	DC.. 0702..
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Centre offset $L_3$	10 mm
ISO code toolholder	AH16Q SDUCR/L07
Pack of insert screws	269028 7
Overall length $L$	180 mm
Clamping height $L_2$	15 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

Set of insert screws Type 7

269028 7

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500