

**Garant**
**Boring bar HSS, right-hand, Shank  $\varnothing$  / insert size: 25/11 mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 260332 25/11  |
| GTIN         | 4045197652966 |
| Item class   | 21T           |

**Technical description**

|  |                               |
|--|-------------------------------|
| Minimum pre-drill $\varnothing D_{\min}$ | 32 mm                         |
| ISO code toolholder                      | AH25R SDUCR/L11               |
| Overhang $L_1$                           | 125 mm                        |
| Centre offset $L_3$                      | 16 mm                         |
| Pack of insert screws                    | 269028 8                      |
| Insert size                              | 11 mm                         |
| suitable indexable insert                | DC.. 11T3..                   |
| Overall length $L$                       | 200 mm                        |
| Clamping height $L_2$                    | 23 mm                         |
| Setting angle $\kappa$                   | 93 degrees                    |
| Shank $\varnothing D_s$                  | 25 mm                         |
| Standard                                 | Works standard                |
| Application type                         | right-hand                    |
| Boring depth up to                       | 5xD                           |
| Tool material                            | HSS                           |
| Through-coolant                          | yes                           |
| Application                              | Internal longitudinal turning |

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Set of insert screws Type 8

269028 8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500