


KOMET® Unisix® indexable insert, P40, Designation type W29: 34-010

Order data

Order number	236760 34-010
GTIN	4047109058972
Item class	24T

Description
Suitable for :

No. 236650; 236660; 236685; 236686

Note:

The standard application values refer to the KUB Trigon®.

Type: ST900

ISO code indexable insert: WOEX 06T304

Feed f in steel < 900 N/mm²: 0.15 mm/rev.

Technical description

Designation	34-010
Feed f in steel < 900 N/mm ²	0.15 mm/rev.
ISO code indexable insert	WOEX 06T304
Grade	P40
Type	ST900
Tool material	Carbide
Type of product	Indexable insert for drilling

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	300 m/min	P
Steel < 750 N/mm ²	suitable	250 m/min	P
Steel < 900 N/mm ²	suitable	200 m/min	P
wet maximum	suitable		