

**Modular vice, Jaw width A: 200/3mm****Order data**

Order number	362110 200/3
GTIN	4067263107149
Item class	32P

**Description****Version:**

- **Machine vice with pull-down jaws.**
- **Simple mechanical actuation (up to 3.5 t).**
- **Easy adjustment of jaw opening.**
- **Case-hardened HRC 60.**
- **Parallelism 0.02 mm.**

**Supplied with:**

Component backstop, 2 T-nuts similar to No. 362160 size 18/16, 1 clamping wrench, 1 L-wrench for hexagon socket screws, 4 clamping claws.

**Note:**

See No. 362160 for other T-nuts.

**Technical description**

Longitudinal tenon slot l	16 mm
Overall length L	595 mm
Transverse tenon slot n	16 mm
Jaw height C	65 mm
Clamping range b	300 mm
Jaw width A	200 mm
Colour code for suitable accessories	Gerardi 200
Weight	69 kg
Base body height G	70 mm
Type of product	Machine vice

