



Modular vice, Jaw width A: 200/4mm

Order data

Order number	362110 200/4
GTIN	4067263107156
Item class	32P

Description

Version:

- Machine vice with pull-down jaws.
- Simple mechanical actuation (up to 3.5 t).
- Easy adjustment of jaw opening.
- Case-hardened HRC 60.
- Parallelism 0.02 mm.

Supplied with:

Component backstop, 2 T-nuts similar to No. 362160 size 18/16, 1 clamping wrench, 1 L-wrench for hexagon socket screws, 4 clamping claws.

Note:

See No. 362160 for other T-nuts.

Technical description

Clamping range b	400 mm
Weight	74 kg
Base body height G	70 mm
Longitudinal tenon slot l	16 mm
Colour code for suitable accessories	Gerardi 200
Transverse tenon slot n	16 mm
Jaw height C	65 mm
Jaw width A	200 mm
Overall length L	695 mm
Type of product	Machine vice

