

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 40/11 mm

Order data

Order number	260342 40/11
GTIN	4045197656056
Item class	21T

Technical description

Shim	269005 3
Pack of insert screws	269028 2
ISO code toolholder	A40T SDUCR/L11
Centre offset L_3	27 mm
Shim screw	269013 2
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Overall length L	300 mm
Clamping height L_2	39 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Set of insert screws Type 8

269028 8

Shim Type 3

269005 3

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500