

**Garant**
**Boring bar steel, left-hand, Shank  $\varnothing$  / insert size: 40/11 mm**

**Order data**

Order number	260343 40/11
GTIN	4045197656025
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	49 mm
suitable indexable insert	DC.. 11T3..
Shim	269005 3
Insert size	11 mm
Shim screw	269013 2
Pack of insert screws	269028 2
ISO code toolholder	A40T SDUCR/L11
Centre offset $L_3$	27 mm
Overall length $L$	300 mm
Clamping height $L_2$	39 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 8	269028 8
Shim Type 3	269005 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500