



Boring bar set, steel, with IC, right-hand, Type: SET11



Order data

Order number	260346 SET11
GTIN	4045197657749
Item class	29W

Description

Supplied with:

Plastic case

Through-coolant: yes

ISO code toolholder: A25R SDUCR/L11

ISO code toolholder: A16Q SDUCR/L11

ISO code toolholder: A20R SDUCR/L11

suitable indexable insert: DC.. 11T3..

Minimum pre-drill $\varnothing D_{\min}$: 25 mm

Minimum pre-drill $\varnothing D_{\min}$: 27 mm

Technical description

Pack of insert screws	269028 8
ISO code toolholder	A25R SDUCR/L11
ISO code toolholder	A16Q SDUCR/L11
ISO code toolholder	A20R SDUCR/L11
suitable indexable insert	DC.. 11T3..

Clamping height L ₂	15 mm
Clamping height L ₂	18 mm
Clamping height L ₂	23 mm
Centre offset L ₃	13.6 mm
Centre offset L ₃	16 mm
Centre offset L ₃	18.5 mm
Minimum pre-drill Ø D _{min}	25 mm
Minimum pre-drill Ø D _{min}	27 mm
Minimum pre-drill Ø D _{min}	32 mm
Overall length L	180 mm
Overall length L	200 mm
Overall length L	200 mm
Application type	right-hand
Boring depth up to	3×D
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws Type 14	269028 14
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws 10 pieces	269420
Boring bar steel Shank Ø / insert size 25/11 mm	260342 25/11
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500