



Boring bar set, steel, with IC, left-hand, Type: SET11



Order data

Order number	260347 SET11
GTIN	4045197657763
Item class	29W

Description

Supplied with:

Plastic case

Through-coolant: yes

ISO code toolholder: A16Q SDUCR/L11

ISO code toolholder: A20R SDUCR/L11

ISO code toolholder: A25R SDUCR/L11

suitable indexable insert: DC.. 11T3..

Minimum pre-drill $\varnothing D_{\min}$: 25 mm

Minimum pre-drill $\varnothing D_{\min}$: 27 mm

Technical description

Pack of insert screws	269028 8
ISO code toolholder	A16Q SDUCR/L11
ISO code toolholder	A20R SDUCR/L11
ISO code toolholder	A25R SDUCR/L11
suitable indexable insert	DC.. 11T3..

Clamping height L ₂	15 mm
Clamping height L ₂	18 mm
Clamping height L ₂	23 mm
Minimum pre-drill Ø D _{min}	25 mm
Minimum pre-drill Ø D _{min}	27 mm
Minimum pre-drill Ø D _{min}	32 mm
Centre offset L ₃	13.6 mm
Centre offset L ₃	16 mm
Centre offset L ₃	18.5 mm
Overall length L	180 mm
Overall length L	200 mm
Overall length L	200 mm
Application type	left-hand
Boring depth up to	3×D
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 14	269028 14
Set of insert screws 10 pieces	269420
Boring bar steel Shank Ø / insert size 16/07 mm	260343 16/07
Boring bar steel Shank Ø / insert size 16/07 mm	260342 16/07
Boring bar steel Shank Ø / insert size 20/11 mm	260343 20/11
Boring bar steel Shank Ø / insert size 25/11 mm	260343 25/11

Boring bar steel Shank Ø / insert size 20/11 mm	260342 20/11
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500