

Garant GRIDLINE

Fold-down front Width 26G, Front height: 275mm**Order data**

Order number	998250 275
GTIN	4067263107958
Item class	91R

Description**Version:**

Fold-down front prevents objects from falling off the shelf. The front can be folded down forwards. Folding angle max. 180°. With aluminium handle with labelling strips that can be exchanged and rewritten. Double-sided locking with one-hand individual drawer release system.

Suitable for:

Shelving systems, container equipment.

Colour:

RAL 7016 anthracite, **powder-coated**.

Note:

A shelf with a front height of at least 50 mm must be installed. When installing drawers with locks, doors, safety locking rod, etc. below the fold-down front, a shelf with a front height of 100 mm is required. Drawer installation is not possible behind the folding front. Not compatible with tool cabinets from group 93.

Technical description

Usable width	650 mm
Usable width in G	26
Folding angle	180 degrees
Usable height	250 mm
Depth	38 mm
Material thickness	1.5 mm
Front height	275 mm

Individual drawer release system	One-hand
Weight	3.2 kg
Application range	Drawer/shelf combination unit
Application range	Container equipment
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Height adjustment interval	25 mm
Type of product	Front flap