

Garant GRIDLINE

Fold-down front Width 26G, Front height: 250mm**Order data**

Order number	998250 250
GTIN	4067263107941
Item class	91R

Description**Version:**

Fold-down front prevents objects from falling off the shelf. The front can be folded down forwards. Folding angle max. 180°. With aluminium handle with labelling strips that can be exchanged and rewritten. Double-sided locking with one-hand individual drawer release system.

Suitable for:

Shelving systems, container equipment.

Colour:

RAL 7016 anthracite, **powder-coated**.

Note:

A shelf with a front height of at least 50 mm must be installed. When installing drawers with locks, doors, safety locking rod, etc. below the fold-down front, a shelf with a front height of 100 mm is required. Drawer installation is not possible behind the folding front. Not compatible with tool cabinets from group 93.

Technical description

Weight	3 kg
Depth	38 mm
Usable height	225 mm
Individual drawer release system	One-hand
Front height	250 mm
Usable width	650 mm
Usable width in G	26

Material thickness	1.5 mm
Folding angle	180 degrees
Application range	Drawer/shelf combination unit
Application range	Container equipment
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Height adjustment interval	25 mm
Type of product	Front flap