

Garant GRIDLINE

**Fold-down front Width 56G, Front height: 250mm****Order data**

Order number	998253 250
GTIN	4067263111559
Item class	91R

**Description****Version:**

Fold-down front prevents objects from falling off the shelf. The front can be folded down forwards. Folding angle max. 180°. With aluminium handle with labelling strips that can be exchanged and rewritten. Double-sided locking with one-hand individual drawer release system.

**Suitable for:**

Shelving systems, container equipment.

**Colour:**

RAL 7016 anthracite, **powder-coated**.

**Note:**

A shelf with a front height of at least 50 mm must be installed. When installing drawers with locks, doors, safety locking rod, etc. below the fold-down front, a shelf with a front height of 100 mm is required. Drawer installation is not possible behind the folding front. Not compatible with tool cabinets from group 93.

**Technical description**

Material thickness	1.5 mm
Usable height	225 mm
Front height	250 mm
Usable width	1400 mm
Depth	38 mm
Usable width in G	56
Weight	5.2 kg

Individual drawer release system	One-hand
Folding angle	180 degrees
Application range	Drawer/shelf combination unit
Application range	Container equipment
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Height adjustment interval	25 mm
Type of product	Front flap