

Garant GRIDLINE

Pull-out shelf with eyelets 200 kg, 26×24G, Installation height: 150mm**Order data**

Order number	998276 150
GTIN	4067263111665
Item class	91R

Description**Version:**

Pull-out shelf with **100% full extension**. Open in front, shell height at sides 46 mm, installation height 150 mm. Without slots to take slotted dividers. Aluminium handle with labelling strips that can be exchanged and rewritten. On the front and back with eyelets for fastening e.g. lashing straps. With one-handed individual drawer release system.

Suitable for:

Shelving systems, container equipment.

Supplied with:

Pull-out shelves each complete with 1 pair drawer runner rails and eyelets.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Not compatible with tool cabinets from group 93, can only be installed in shelving system.

Technical description

Installation height	150 mm
Application range	Container equipment
Drawer usable area in G	26×24
Usable width in G	26
Individual drawer release system	One-hand
Number of eyelets	4

Usable depth in G	24
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Usable width	650 mm
Usable depth	600 mm
Type of product	Pull-out shelf