

Garant GRIDLINE

Pull-out shelf with eyelets, 200 kg, 36×20G, Installation height: 150mm**Order data**

Order number	998275 150
GTIN	4067263111658
Item class	91R

Description**Version:**

Pull-out shelf with **100% full extension**. Open at the front, shell height at sides 46 mm, installation height 150 mm. Without slots to take slotted dividers. Aluminium handle with labelling strips that can be exchanged and rewritten. On the front and back with eyelets for fastening e.g. lashing straps. With one-handed individual drawer release system.

Suitable for:

Shelving systems, container equipment.

Supplied with:

Pull-out shelves each complete with 1 pair drawer runner rails and eyelets.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Not compatible with tool cabinets from group 93, can only be installed in shelving system.

Technical description

Application range	Container equipment
Installation height	150 mm
Usable width in G	36
Number of eyelets	4
Drawer usable area in G	36×20
Individual drawer release system	One-hand

Data sheet

Usable depth in G	20
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Product name attribute	36×20G
Usable width	900 mm
Usable depth	500 mm
Type of product	Pull-out shelf