

Garant GRIDLINE

Pull-out shelf with eyelets 200 kg, 56×24G, Installation height: 150mm



Order data

Order number	998280 150
GTIN	4067263111702
Item class	91R

Description

Version:

Pull-out shelf with **100% full extension**. Open in front, shell height at sides 46 mm, installation height 150 mm. Without slots to take slotted dividers. Aluminium handle with labelling strips that can be exchanged and rewritten. On the front and back with eyelets for fastening e.g. lashing straps. With one-handed individual drawer release system.

Suitable for:

Shelving systems, container equipment.

Supplied with:

Pull-out shelves each complete with 1 pair drawer runner rails and eyelets.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Not compatible with tool cabinets from group 93, can only be installed in shelving system.

Technical description

Installation height	150 mm
Application range	Container equipment
Individual drawer release system	One-hand
Drawer usable area in G	56×24
Number of eyelets	8
Usable width in G	56
Usable depth in G	24

Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	56×24G
Usable width	1400 mm
Usable depth	600 mm
Type of product	Pull-out shelf