

HEDI

Machine / workstation lamp, Type: 20B



Order data

Order number	081300 20B
GTIN	4003644014309
Item class	08B

Description

Version:

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

Robust, long, coated flexible metal arm for good mobility of the lamp head and high stability. 20 or 50 Watt **halogen flood beam** with reflector.

Standard:

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

- **Sturdy, long, coated flexible metal arm.**

Supplied with:

Bulb, with **strong magnetic clamp, 50 mm screw-on clamp, and mounting screws** for machine, table, wall or ceiling attachment.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

IP Index of Protection: IP 20

Light output: 20 W

Illumination: 190 lm

Connection cable length: 3 m

Energy efficiency class : B

Technical description

Energy efficiency class	B
Illumination	190 lm
Connection cable length	3 m
Light colour	3,000 K
Power supply	Mains-powered
Bulb	Halogen
IP Index of Protection	IP 20
Lamp replaceable	yes
Light output	20 W

Accessories

Spare bulb suitable for type 20B	081310 20B
----------------------------------	------------