


**KOMET® Unisix® indexable insert, BK8425, Designation type W29: 58-010**

**Order data**

Order number	236840 58-010
GTIN	4047109178250
Item class	24T

**Description**
**Suitable for :**

No. 236685; 236686

**Note:**

**The standard application values refer to the KUB Trigon®.**

Type: ST1400

ISO code indexable insert: WOEX 120608

Feed f in steel < 900 N/mm<sup>2</sup>: 0.2 mm/rev.

**Technical description**

Designation	58-010
Feed f in steel < 900 N/mm <sup>2</sup>	0.2 mm/rev.
ISO code indexable insert	WOEX 120608
Grade	BK8425
Type	ST1400
Tool material	Carbide
Type of product	Indexable insert for drilling

## User data

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 500 N/mm <sup>2</sup>	suitable	300 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	250 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	200 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	130 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	160 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	160 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	S
wet maximum	suitable		
dry	suitable only under restricted conditions		