


HOLEX Pro screw-on toolholder, right-hand, Shank / insert size: 20/09mm

Order data

Order number	260048 20/09
GTIN	4067263109624
Item class	22E

Description
Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Standard	Works standard
Overall length L	125 mm
Functional width L ₄	25 mm
Insert size	9 mm
Pack of insert screws	269028 2
ISO code toolholder	SCLCR/L 2020K09
Shank size	20 mm
suitable indexable insert	CC.. 09T3..
Head length L ₁	17 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15