



## HOLEX Pro screw-on toolholder, right-hand, Shank / insert size: 25/09mm



### Order data

Order number	260048 25/09
GTIN	4067263109631
Item class	22E

### Description

#### Version:

Targeted cooling on the cutting edge.

#### Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

### Technical description

Insert size	9 mm
ISO code toolholder	SCLCR/L 2525M09
Head length L <sub>1</sub>	19 mm
Pack of insert screws	269028 2
Overall length L	150 mm
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	CC.. 09T3..
Standard	Works standard
Shank size	25 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15