



HOLEX Pro screw-on toolholder, right-hand, Shank / insert size: 20/11 mm



Order data

Order number	260304 20/11
GTIN	4067263109662
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Shank size	20 mm
Insert size	11 mm
Standard	Works standard
Overall length L	125 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 2
Functional width L ₄	25 mm
ISO code toolholder	SDJCR/L 2020K11
Head length L ₁	20.5 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15