



HOLEX Pro screw-on toolholder, left-hand, Shank / insert size: 20/11mm



Order data

Order number	260305 20/11
GTIN	4067263109686
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Standard	Works standard
Overall length L	125 mm
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Shank size	20 mm
Pack of insert screws	269028 2
Functional width L ₄	25 mm
Head length L ₁	20.5 mm
ISO code toolholder	SDJCR/L 2020K11
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15