


HOLEX Pro screw-on toolholder, left-hand, Shank / insert size: 20/11mm

Order data

Order number	261301 20/11
GTIN	4067263109440
Item class	22E

Description
Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G 1/8 inch – included in delivery).

Technical description

Standard	Works standard
suitable indexable insert	VC.. 1103..
Insert size	11 mm
Head length L ₁	24 mm
Pack of insert screws	269028 22
Overall length L	125 mm
Shank size	20 mm
Functional width L ₄	25 mm
ISO code toolholder	SVJCR/L 2020K11
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver Type TX15	659950 TX15
Torque screwdriver Type TX8	659950 TX8