



HOLEX Pro screw-on toolholder, right-hand, Shank / insert size: 20/11 mm



Order data

Order number	261300 20/11
GTIN	4067263109426
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G 1/8 inch – included in delivery).

Technical description

Functional width L_4	25 mm
Head length L_1	24 mm
Overall length L	125 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVJCR/L 2020K11
Standard	Works standard
Shank size	20 mm
Pack of insert screws	269028 22
Insert size	11 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver Type TX15	659950 TX15
Torque screwdriver Type TX8	659950 TX8