



## HOLEX Pro screw-on toolholder, left-hand, Shank / insert size: 25/11mm



### Order data

Order number	261301 25/11
GTIN	4067263109457
Item class	22E

### Description

#### Version:

Targeted cooling on the cutting edge.

#### Note:

Coolant transfer under the head via hose connection (G 1/8 inch – included in delivery).

### Technical description

Pack of insert screws	269028 22
Overall length L	150 mm
Functional width L <sub>4</sub>	32 mm
Shank size	25 mm
Standard	Works standard
ISO code toolholder	SVJCR/L 2525M11
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Head length L <sub>1</sub>	26 mm
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver Type TX15	659950 TX15
Torque screwdriver Type TX8	659950 TX8