

Garant**Side lock arbor, PSC 32 short, Clamping \varnothing D1: 6mm****Order data**

Order number	308496 6
GTIN	4067263110002
Item class	31A

Description**Version:**

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Note:

Suitable reducing adapter from SK 40 or HSK 63 to PSC32, PSC 40 or PSC 50 on request.
Suitable reducing adaptor from SK 50 or HSK 100 to PSC 63 or PSC 80 on request.

Technical description

Overhang dimension A	45 mm
Clamping \varnothing D ₁	6 mm
External \varnothing D	25 mm
Adapter	PSC 32 short
Arbor standard	ISO 26623-1
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor