

Garant
Shrink-fit chucks with cooling channel bore, PSC 32 short, Clamping \varnothing D1: 10mm

Order data

Order number	308559 10
GTIN	4067263110064
Item class	31A

Description
Version:

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

With coolant channel bores and threads that can be sealed. The internal and external thread correspond to the size.

Application:

For clamping tools with shank tolerance h6.

Optional extras:

Shrink-fit chuck extensions No. 302410 – 302416. Shrink-fitting units No. 354210 – 354400. Balancing screws set No. 309906 size 180.

Technical description

External \varnothing D	32 mm
Overhang dimension A	70 mm
Clamping \varnothing D ₁	10 mm
\varnothing D ₂	24 mm
Cooling channel bore	lockable
Adapter	PSC 32 short

Arbor standard	ISO 26623-1
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chucks