

Garant**Arbor for screw-in milling cutter, cylindrical, PSC 63, Thread size M: M10X50****Order data**

Order number	308553 M10X50
GTIN	4067263110095
Item class	31A

Description**Version:**

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

To take screw-in milling cutters with thread.

Technical description

Overhang dimension A	74.5 mm
Bore $\varnothing D_1$	10.5 mm
Reach L_1	50 mm
External $\varnothing D$	18 mm
Thread M	M10x50
Adapter	PSC 63
Arbor standard	ISO 26623-1
Through-coolant	yes
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy	HPC
Type of product	Threaded copy mill arbor