

**Electronics snipe-nosed pliers, angled 45°, overall length: 145mm****Order data**

Order number	727193 145
GTIN	4003773039396
Item class	73F

**Description****Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Precision box joint. Low-friction double spring for smooth and gentle opening. Gripping faces ground smooth. Edges carefully deburred.

Handles with multi-component coating.

**Application:**

For precision assembly work, e.g. in electronics and precision mechanisms.

**Standard:**

DIN ISO 9655

**Material:**

Ball-bearing steel, oil quenched.

**Note:**

Further versions available on request.

**Technical description**

overall length	145 mm
Jaw length	35 mm
Head width	12 mm
Jaw design	tapering to a point, 45° angled
Standard	DIN ISO 9655
Type of jaws	inside ground smooth

Handle	Multi-component covering
Material	Ball bearing steel
Surface	mirror polished
with return spring	yes
Type of product	Snipe nose pliers