

**LED rechargeable work light, Type: 205****Order data**

Order number	081567 205
GTIN	4067263110804
Item class	02A

Description**Version:**

LED rechargeable work lamp with 2 brightness levels and spotlight (100 lumens). With suspension hook, folding stand and USB-C charging port.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Charging cable.

Technical description

Power supply	Mains operated
Number of rechargeable batteries contained	1
Illumination time	3 - 6.5 h
Weight	201 g
Bulb	LED module

Data sheet

Illumination	350 lm
IP Index of Protection	IP 65
Light colour	cold white
Type of rechargeable battery	Lithium-ion
Illumination step 2	150 lm
Overall length	205 mm
Type of product	Work lamp