

**KOMET® Unisix® indexable insert, BK62, Designation type W29: 10-010****Order data**

Order number	236780 10-010
GTIN	4047109058545
Item class	24T

Description**Suitable for :**

No. 236630; 236635; 236650

Note:**The standard application values refer to the KUB Trigon®.**

Type: GG(G)

ISO code indexable insert: WOEX 030204

Feed f in steel < 900 N/mm²: 0.08 mm/rev.**Technical description**

Designation	10-010
Feed f in steel < 900 N/mm ²	0.08 mm/rev.
ISO code indexable insert	WOEX 030204
Grade	BK62
Type	GG(G)
Tool material	Carbide
Type of product	Indexable insert for drilling

User data

	Suitability	V_c	ISO code
GG(G)	suitable	200 m/min	K
wet maximum	suitable		