

Garant**Arbor, SK 40, ABS® Ø d: 50mm**

Order data

Order number	238420 50
GTIN	4067263110910
Item class	29W

Description

Supplied with:**Complete with sealing washer and conversion set for form AD.****Note:**

Further arbors with ABS® connection on request.

Technical description

Overhang A	50 mm
Projection length L ₁	30 mm
ABS® Ø d	50 mm
Adapter	SK 40
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting

