

Garant**Arbor, HSK-A 63, ABS® Ø d: 40mm**

Order data

Order number	238500 40
GTIN	4067263111009
Item class	29W

Description

Version:

- Arbor balanced to Q 6.3 at 10,000 rpm.
- With through coolant feed.

Standard:**DIN 69893****Note:**

Further arbors with ABS® connection on request.

Technical description

Projection length L ₁	34 mm
Overhang A	60 mm
ABS® Ø d	40 mm
Adapter	HSK-A 63
Shank	ABS
Arbor standard	DIN 69893
Through-coolant	yes
External Ø d ₁	63 mm

Type of product

ABS mounting