

**Garant****Arbor, SK 50, ABS® Ø d: 100mm**

## Order data

Order number	238440 100
GTIN	4067263110934
Item class	29W

## Description

**Supplied with:****Complete with sealing washer and conversion set for form AD.****Note:**

Further arbors with ABS® connection on request.

## Technical description

Overhang A	115 mm
Projection length L <sub>1</sub>	95 mm
ABS® Ø d	100 mm
Adapter	SK 50
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting

