

Garant**Arbor, SK 50, ABS® Ø d: 40mm**

Order data

Order number	238440 40
GTIN	4067263110941
Item class	29W

Description

Supplied with:**Complete with sealing washer and conversion set for form AD.****Note:**

Further arbors with ABS® connection on request.

Technical description

Projection length L ₁	20 mm
Overhang A	60 mm
ABS® Ø d	40 mm
Adapter	SK 50
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting

