

**Garant****Arbor, HSK-A 100, ABS® Ø d: 40mm**

## Order data

Order number	238520 40
GTIN	4067263111030
Item class	29W

## Description

**Version:**

- Arbor balanced to Q 6.3 at 10,000 rpm.
- With through coolant feed.

**Standard:****DIN 69893****Note:**

Further arbors with ABS® connection on request.

## Technical description

Overhang A	80 mm
Projection length L <sub>1</sub>	51 mm
ABS® Ø d	40 mm
Adapter	HSK-A 100
Shank	ABS
Arbor standard	DIN 69893
Through-coolant	yes
External Ø d <sub>1</sub>	100 mm

Type of product

ABS mounting