

Garant
Arbor, HSK-A 100, ABS® Ø d: 80mm


Order data

Order number	238520 80
GTIN	4067263111061
Item class	29W

Description

Version:

- Arbor balanced to Q 6.3 at 10,000 rpm.
- With through coolant feed.

Standard:
DIN 69893
Note:

Further arbors with ABS® connection on request.

Technical description

Overhang A	90 mm
Projection length L ₁	61 mm
ABS® Ø d	80 mm
Adapter	HSK-A 100
Shank	ABS
Arbor standard	DIN 69893
Through-coolant	yes
External Ø d ₁	100 mm

Type of product

ABS mounting